

## INOFLON® M295

### TECHNICAL DATA SHEET

#### TECHNICAL INFORMATION

INOFLON® M295 is a next-generation free flow moulding grade resin which is chemically modified to give superior performance than standard PTFE. Its significantly lower melt viscosity than standard PTFE gives better particle fusion during sintering and smoother surfaces result in improved performance.

INOFLON® M295 is designed for compression moulding of blocks and sheets, automated and iso-static moulding. It can be used preferably in applications such as seal rings, valve seats, or bearing pads. The improved barrier properties make the material to be the ideal solution for pressure house bearings, linings, and encapsulations, etc.

#### PRODUCT FEATURES

- Low permeability and void content
- Good mould filling behaviour
- Better transparency
- Low deformation under load
- Good weldability
- Good electrical and mechanical properties

#### TYPICAL PROPERTIES

Properties	Test Method	Unit	Nominal Value
Bulk density	ASTM D 4894	g/l	700
Average particle size (d <sub>50</sub> )	ASTM D 4894	µm	475
Mould shrinkage	ASTM D 4894	%	4.0
Powder flow	ASTM D 1895	g/min	350
Std. specific gravity (SSG)	ASTM D 4894	-	2.160
Melting points	ASTM D 4894	°C (°F)	342 (648) Initial 327 (621) Final
Tensile strength	ASTM D 4894	MPa (psi)	30 (4351)
Elongation	ASTM D 4894	%	400
Deformation under load (14 MPa)	ASTM D 621	%	4.1
Dielectric strength	ASTM D 149	kV/mm	80

Note: These are typical properties and not to be used for specification purposes.

#### FDA COMPLIANCE

When products made from INOFLON® M295 are correctly processed, that is sintered at high temperature practiced by industries, they may comply with FDA Regulation 21 CFR 177.1550 for use in contact with food.

#### PACKAGING

INOFLON® M295 is packed in 25 and 40 kg plastic drums.

# INOFLON® M295

## HANDLING AND STORAGE

INOFLON® M295 is being produced in a clean environment and therefore the ideal resin for all applications, where superior cleanliness is required, especially such as production, storage, and transportation of ultrapure chemicals for semiconductor production. Therefore for best results, the powder processing areas should be kept clean and free of all contamination. Organic contamination and foreign matter usually appear as dark spots often easily visible against the translucent Modified PTFE background. Organic contamination material degrades at the sintering temperatures and forms discolored spots. They oxidize away as carbon dioxide wherever sufficient oxygen exposure takes place. To avoid contamination and discoloration throughout the whole INOFLON® products, it is recommended to process the modified INOFLON® grades under special cleanliness precautions. This is required for those production areas, where the product is handled as a powder. As soon as the billet is moulded the cleanliness of the powder can be considered to be 'protected'. Storage of PTFE at 23°C (73.4°F) or lower prevents lump formation as a result of movement and transportation.

## PROCESSING

INOFLON® M295 is processed using automatic, isostatic, and compression moulding methods. A two-step process is used to fabricate parts from INOFLON® M295. Before using, the powder must be conditioned above 19°C(66.2°F). Firstly, the mould is filled with resin and compacted into a preform that is similar to the final shape of the desired moulding. Preforming is easiest when the resin temperature is uniform between 21-27°C (69.8-80.6°F). As temperature declines below this range, the resin will be increasingly difficult to mould without cracks due to the problem of condensed moisture. The preform is then sintered in an oven where it undergoes controlled heating and cooling cycle. The two cycles together are commonly called sintering cycle and peak holding temperature is called sintering temperature. The sintering temperature should be in the range of 370-375°C (698-707°F). INOFLON® M295 is also processed by ram extrusion, in which preforming and sintering steps are combined in a continuous operation. Large diameter rods and tubings are fabricated by feeding successive charges of powder down a cylindrical heated die using a defined temperature profile.

## SAFETY PRECAUTIONS

Handling and processing of PTFE must be done in ventilated areas to prevent personnel exposure to the fumes liberated during sintering and heating of the resin. Fumes should not be inhaled and eye and skin contact must be avoided. In case of skin contact wash with soap and water immediately. In case of eye contact, flush with water immediately and seek medical help. Smoking tobacco or cigarettes contaminated with PTFE may result in a flu-like condition including chills, fever and sore throat that may not occur until a few hours after exposure has taken place.

Mixtures of some metal powders such as magnesium or aluminum are flammable and explosive under some conditions. Please read the Material Safety Data Sheet and the detailed information in the "Guide for the Safe Handling of Fluoropolymer Resins" available at [www.plasticseurope.org](http://www.plasticseurope.org).

INOFLON® is the brand name of Gujarat Fluorochemicals Limited (GFL) used for its brand of fluoropolymer resin. INOFLON® can be used in applications duly approved by GFL. Customers who plan to use the word INOFLON® as the trademark on or relation to their fluoropolymer parts and other products in any style or combination or any manner whatsoever must contact GFL for prior permission for such use. No consumer/user of GFL fluoropolymer resin is permitted to claim that their products contain INOFLON® without prior permission from GFL.

The information provided in the bulletin is furnished at no cost to the recipient and is based on the information and technical data that Gujarat Fluorochemicals Limited believes is correct and sound. Those who choose to use the information must be technically qualified, and do so entirely at their own cost and risk. The users must determine and ensure that their specific conditions of processing present no health or safety hazards. GFL does not warranty, either expressly or impliedly in respect of the use of this information for application of its INOFLON® branded fluoropolymer resin and shall bear no liability as a result of any loss or damage caused directly or indirectly due to use of any information provided in this bulletin. Nothing contained herein can be taken or construed as a grant of license by GFL to operate under or a recommendation to infringe any patents.

WARNING: Do not use any of INOFLON® PTFE resins in medical devices that are designed for permanent implantation in the human body. For other medical uses, prior permission of GFL may be sought.

## SALES AND TECHNICAL SUPPORT

### Corporate & Marketing Headquarter

Gujarat Fluorochemicals Limited  
INOX Towers, 17, Sector-16A,  
Noida - 201301 U.P., India  
+91 120 6149600

### Europe

Gujarat Fluorochemicals GmbH  
Regus Center Watermark 14<sup>th</sup> Floor,  
Überseeallee 10, 20457 Hamburg, Germany  
+49 40 808074-667/668

### Works

Gujarat Fluorochemicals Limited  
12/A Dahej, GIDC, Industrial Estate,  
Tehsil Vagra, Dist. Bharuch 392130, Gujarat, India  
+91 2641 618003

### Americas

GFL Americas, LLC  
1212 Corporate Dr., Suite-540,  
Irving, TX 75038, USA  
+1 512 446 7700

